

HDTB

Hygienic Design, Terminal Box



Material: AISI 304L pre-grained stainless steel. Body and cover: 1.5 mm.

Body: Folded and seam welded. Four M6x13 studs for bottom profile / mounting plate fixation.

Cover: Folded and seam welded. Sides sloped at 3°. AISI 316 HD bolts with blue silicone gasket included.

Gasket: A one piece removable silicone gasket with molded corners helps ensure proper sealing, and makes removing and replacing it faster and easier for cleaning and maintenance operations. The silicone is FDA 21 CFR 177.2600 compliant. Colour blue (RAL 5010).

Cable access: No gland openings as standard to minimize hygiene risks.

Earthing: M8x18 mm earthing studs in body and cover, M8 nuts, earthing washers and earthing labels.

Protection: Corresponds with IP 66/69 | TYPE 4X, 13 | IK08.

Finish: 400 pre-grained stainless steel, polished to Ra < 0.8 µm.

Delivery: Body with cover and mounting accessories.

Additional information: For accessories on the outside of the enclosure, please see our HD accessories section.

H	W	D	Item no.
150	150	80	HDTB151508
150	150	120	HDTB151512
200	200	120	HDTB202012
200	300	120	HDTB203012
200	400	120	HDTB204012
300	400	120	HDTB304012