

Power System Module

PSM socket modules

PSM socket modules

Required module slots in PSM busbar	Connector pattern	Slots	Thermal overcurrent protection	Packs of	Model No.
1 Standard socket modules/non-switchable					
1	C13	6	–	1 pc(s).	7856.080
1	C13	6	■	1 pc(s).	7856.070
1	C13	4	■/per output	1 pc(s).	7856.220
1	Earthing-pin 320/CEE 7/4	4	–	1 pc(s).	7856.100
1	Earthing-pin 320/CEE 7/4	4	■	1 pc(s).	7856.090
1	C19	4	–	1 pc(s).	7856.230
1	C13 red	6	–	1 pc(s).	7856.082
1	Earthing-pin, red	4	–	1 pc(s).	7856.240
2 Socket modules, international					
1	France/Belgium/CEE 7/5	4	–	1 pc(s).	7856.120
1	Switzerland	5	–	1 pc(s).	7856.190
3 Socket modules with LED display/current measurement per module					
1	C13	6	–	1 pc(s).	7859.120
1	C19	4	–	1 pc(s).	7859.130
4 Socket modules with switchable slot/aggregate current measurement per module					
2	C13	8	■	1 pc(s).	7856.201
2	Earthing-pin 320/CEE 7/4/C13	4/2	■	1 pc(s).	7856.203
2	C19/C13	4/2	■	1 pc(s).	7856.204
5 Socket modules with switchable slot/individual current measurement per slot					
2	Earthing-pin 320/CEE 7/4/C13	4/2	■	1 pc(s).	7859.212
2	C13	8	■	1 pc(s).	7859.222
2	C19/C13	4/2	■	1 pc(s).	7859.232

Approvals:

Available on the Internet

