

Cable management

Cable clamp rails

for TS and between the mounting angles of the TS-IT in the enclosure depth

For cable routing on the enclosure frame. The cables may be attached to the cable clamp rails with cable ties or nylon loops. The cable clamp rails are simply located onto the frame section and may additionally be secured with a screw.

Material:

- Sheet steel

Supply includes:

- Assembly parts

For the inner mounting level

For enclosures		Packs of	Model No.
Width mm	Depth mm		
600	600	4 pc(s).	7828.061
800	800	4 pc(s).	7828.081
1000	1000	4 pc(s).	7828.101
1200	1200	4 pc(s).	7828.121

For the outer mounting level

For enclosures		Packs of	Model No.
Width mm	Depth mm		
600	600	4 pc(s).	7828.062
800	800	4 pc(s).	7828.082
1000	1000	4 pc(s).	7828.102
1200	1200	4 pc(s).	7828.122



Accessories:

- Cable ties, see page 667
- Nylon loop, see page 667



Cable clamp rails, depth-variable

for TS and between the mounting angles of the TS-IT in the enclosure depth

For cable routing on the enclosure frame and for strain relief of the routed cables. The cables may be attached to the cable clamp rails with cable ties or nylon loops.

The cable clamp rails may be located horizontally at the rear directly onto a 482.6 mm (19") mounting frame or in the enclosure depth between two mounting frames. An additional screw fastening secures the unit.

The depth variability of the rails facilitates flexible adaptation of their length to the existing attachment distance between the two 482.6 mm (19") mounting levels.

Material:

- Sheet steel

Supply includes:

- Assembly parts

Mounting dimensions ¹⁾ mm	Packs of	Model No.
325 - 575	4 pc(s).	7858.160
500 - 895	4 pc(s).	7858.162

¹⁾ Mounting dimensions + 152 mm = distance between 482.6 mm (19") levels



Accessories:

- Cable ties, see page 667
- Nylon loop, see page 667



Cable clamp, variable

for enclosure-independent mounting

Variable attachment from 450 to 800 mm for flexible cable clamping in two variants.

Supports attachment to punched sections with and without mounting flanges and direct screw-fastening onto mounting plates and other flat surfaces.

Material:

- Sheet steel, zinc-plated

Supply includes:

- Assembly parts

1 C rail

2 T-head rail

Version	Packs of	Model No.
C rail	1 pc(s).	7016.140
T-head rail	1 pc(s).	7016.150

