

With glazed door for rack climate control

U	Packs of	42	42	42	42	47	Page
Width mm		600	800	600	800	800	
Height mm		2000	2000	2000	2000	2200	
Depth mm		1000	1000	1200	1200	800	
Glazed aluminium door at the front (180°), with comfort handle for semi-cylinder and security lock 3524 E	1	■	■	■	■	■	
Sheet steel door at the rear (180°), vertically divided, with comfort handle for semi-cylinder and security lock 3524 E	1	■	■	■	■	■	
482.6 mm (19") mounting level at the front and rear, on depth stays with quick-release fasteners, depth-variable	4	■	■	■	■	■	
Roof plate, multi-piece, removable, with side cable entry in the depth and covered cut-out for fan mounting plate	1	■	■	■	■	■	
Model No. DK	1	5508.120	5509.120	5510.120	5511.120	5512.120	
Included with the supply, not pre-installed							
Spacers for passive cooling	4	■	■	■	■	■	
Earthing set with central earthing point	1 set	■	■	■	■	■	
Multi-tooth screws M5, cage nuts M5, conductive	50	■	■	■	■	■	
Accessories							
Side panels, 2-part	1	2 x 5501.030	2 x 5501.030	2 x 5501.040	2 x 5501.040	2 x 5501.050	28
Base mount	2	5501.320	5501.320	5501.350	5501.350	5501.310	28
Gland plates, modular	see from page 24						
Base/plinth	see Cat. 33, page 542						
Fan mounting plate for TS IT including thermostat	1	5502.010	5502.020	5502.010	5502.020	5502.020	29
Air baffle plate	1 set	5501.805	5501.815	5501.805	5501.815	5501.835	34
Cable route	1	5502.120	5502.120	5502.120	5502.120	5502.120	31
Cable duct	1	–	5502.105	–	5502.105	5502.145	30
Component shelves	see from page 29						
Slide rails	see from page 34						
Cable clamp rails, C rails, punched sections with mounting flanges	see Cat. 33, from page 644						
Cable shunting ring	see Cat. 33, from page 724						
Cable management panel	see page 33						
Power distribution unit PDU	see page 39						

■ Included with the supply.



Rittal Germany

RITTAL GmbH & Co. KG
 Postfach 1662 · D-35726 Herborn
 Phone: +49(0)2772 505-0
 Fax: +49(0)2772 505-2319
 E-mail: info@rittal.de · www.rittal.com