

Base mounting bracket

Brackets for screw-fastening from below to the cast feet with posidrive raised countersunk screws M12. Optionally with projection at the front, interior or sides, with Ø 11 mm hole for screw-fastening to the base.

Material:

- Steel

Surface finish:

- Zinc-plated

Supply includes:

- Posidrive raised countersunk screws M12

Packs of	Model No.
4 pc(s).	6147.000



Trim panel

Material:

- Cast aluminium

Supply includes:

- Assembly parts for screw-fastening between the cast feet at the front or rear

Colour RAL	Model No.
7035 textured	6144.100



Enclosure reinforcement

For external or internal reinforcement of enclosures of a corresponding size. Smaller enclosures may also be mounted directly without reinforcement.

Supply includes:

- Assembly parts for the enclosure and support section plus 2 seals

Technical details

Available on the Internet

	For enclosure	Support arm connection	Material	Weight kg	Model No.
1	B1 ≥ 300 mm, T1 ≥ 150 mm	CP 40, stainless steel	Stainless steel 1.4301	0.9	6143.310
2	B1 ≥ 300 mm, T1 ≥ 150 mm	CP 60	Sheet steel	0.9	6106.110

