



System accessories Page 507 **Monitors, keyboards** Page 706/707 **PC enclosure system, sheet steel** Page 118

PC enclosure systems based on SE, stainless steel 1.4301 (AISI 304), for the secure accommodation of all your computer equipment, from the monitor, computer system, printer, keyboard to the mouse.

Material:

- Enclosure: Stainless steel 1.4301 (AISI 304), 1.5 mm
- Rear door: Stainless steel 1.4301 (AISI 304), 2.0 mm
- Gland plates: Stainless steel 1.4301 (AISI 304), 1.5 mm
- Monitor field: Single-pane safety glass, 4 mm

Surface finish:

- Brushed, grain 400

Protection category IP to IEC 60 529:

- IP 55

Protection category NEMA:

- NEMA 12

Supply includes:

- Enclosure, solid top and sides
- Rear door with locking rod
- Glazed door at the top, latched from the inside
- Component shelf
- Keyboard drawer with swing-down front for handrest and mouse pad support
- Lock insert, lock no. 3524 E
- Bottom door with locking rod
- Cam lock with 3 mm double-bit insert
- Gland plates, divided

Approvals:

- UL
- cUL

Technical details:

Available on the Internet

Stainless steel

Width mm	Packs of	600	Page
Height mm		1600	
Depth mm		630	
Model No.	1 pc(s).	4650.100	
Weight kg		115.0	
Accessories			
Base/plinth components, front and rear, 100 mm	1 set(s)	8701.600	518
Base/plinth trim panels, side, 100 mm	1 set(s)	8701.060	518
Levelling feet	4 pc(s).	2859.000	521
Base/plinth trim, modular	4 pc(s).	2913.000	518
Adaptor pieces, 482.6 mm (19")	4 pc(s).	8613.010	684
Component shelf, pull-out	1 pc(s).	6902.960	627
Cable clamp rails	2 pc(s).	4191.000	665
System lights		from page	634
Lock systems		from page	563