
















Support arm system CP 60

	Rotating/tilting	Rigid	Length mm	Weight kg	Colour RAL	Enclosure section CP 60	Enclosure section CP 60/40	Desk section CP 60	Wall section CP 60	
	Model No.									
Tilting adaptor 10° for support arm connection										
	Ø 130 mm	-	■	-	0.6	7035	6206.400	-	-	-
	□ 120 x 65 mm	-	■	-	0.4		6206.440	-	-	-
Tilting adaptor +/-45°/tilting adaptor +100°/-60° for support arm connection										
	Ø 130 mm	■	-	-	1.2	7024	6206.420	-	-	see page 161/162
	□ 120 x 65 mm	■	-	-	0.8	7035/7024	6206.460	6206.460	-	-
	□ 90 x 71 mm	-	-	-	0.8		-	6206.460	-	-
Connection console VESA 75/100 for support arm connection										
	□ 120 x 65 mm	-	■	-	1.1	7035/7024	6206.480	-	-	see page 156
Attachment CP 60/40 for support arm connection										
	Ø 130 mm	-	■	-	0.7	7035	6206.320	-	-	-
	□ 120 x 65 mm	-	■	-	1.0	7035	6206.360	-	-	-
	□ 90 x 71 mm	-	-	-	1.0	7024	-	6501.070	-	-
Coupling CP 60/40 for support arm connection										
	Ø 130 mm	■	-	-	2.1	7035	6206.300	-	-	-
	□ 120 x 65 mm	■	-	-	1.2	7035	6206.340	6501.130	-	-
	□ 90 x 71 mm	-	-	-	1.1	7024	-	6501.050	-	-
Angle coupling 90° CP 60/40 for support arm connection										
	Ø 130 mm	■	-	-	1.8	7035/7024	6206.380	-	-	-
Support section CP 60/40										
	Solid	-	-	250 500 1000 2000	1.25 2.5 5.0 10.0	7035	6206.025 6206.050 6206.100 6206.200	CP 60 CP 40 ¹⁾ - 6501.000 6501.020 -	CP 60 CP 60 6206.025 6206.050 6206.100 6206.200	CP 60 CP 60 6206.025 6206.050 6206.100 6206.200
Angle adaptor 90° for support arm combination CP 60/40										
		-	■	-	1.0	7035/7024	-	6206.640	-	see page 158
Angle piece 90°, CP 60										
		-	■	-	0.5	7035/7024	6206.600	-	-	6206.600
Intermediate hinge CP 60										
		■	-	-	2.2	7035/7024	-	-	6206.620	-
Top-mounted joint CP 60										
	Horizontal outlet	■	-	-	2.2	7035/7024	-	-	-	6206.700
Wall-mounted hinge CP 60										
	Horizontal outlet	■	-	-	2.85	7035/7024	-	-	-	6206.740
Wall/base mounting bracket CP 60, small										
		-	■	-	0.35	7035	-	-	-	6206.820
Wall/base mounting bracket CP 60, large										
		-	■	-	1.4	7035/7024	-	-	-	6206.800
Mounting component CP 60 for signal pillar										
		-	■	-	0.1	7024	6206.900	6206.900	6206.900	see page 720 6206.900
Accessories										
	Adaptor CP 120/60 Ø 130 mm to □ 120 x 65 mm									6212.500 see page 157

¹⁾ Weight information and diagrams for CP 40, see page 139