


# Busbar systems Flat-PLS

## System components

Connection system	Flat-PLS 60		Flat-PLS 100			
	Model No. SV		Model No. SV			
	<b>A Connection brackets</b> for Flat-PLS For connecting the connection kits of open air circuit-breakers to a Flat-PLS 60/100 main bar system in the roof section, base section, directly above or below the air circuit-breaker.					
	For bar width of connection brackets mm	No. of strands per conductor	For conductor	For enclosure depth mm	Packs of	
60	1	L1, L2, L3	600	1 set	<b>9676.201</b>	<b>9676.301</b>
		N		1 set	<b>9676.202</b>	–
	2	L1, L2, L3		1 set	<b>9676.203</b>	<b>9676.303</b>
		N		1 set	<b>9676.204</b>	–
	3	L1, L2, L3		1 set	<b>9676.205</b>	<b>9676.305</b>
		N		1 set	<b>9676.206</b>	–
100	2	L1, L2, L3	1 set	<b>9676.213</b>	<b>9676.313</b>	
		N	1 set	<b>9676.214</b>	–	
	3	L1, L2, L3	1 set	<b>9676.215</b>	<b>9676.315</b>	
120	2	L1, L2, L3	1 set	<b>9676.216</b>	–	
		N	1 set	<b>9676.217</b>	<b>9676.317</b>	
	3	L1, L2, L3	1 set	<b>9676.218</b>	–	
60	1	L1, L2, L3	800	1 set	<b>9676.221</b>	<b>9676.321</b>
		N		1 set	<b>9676.222</b>	<b>9676.322</b>
	2	L1, L2, L3		1 set	<b>9676.223</b>	<b>9676.323</b>
		N		1 set	<b>9676.224</b>	<b>9676.324</b>
	3	L1, L2, L3		1 set	<b>9676.225</b>	<b>9676.325</b>
		N		1 set	<b>9676.226</b>	<b>9676.326</b>
100	2	L1, L2, L3	1 set	<b>9676.233</b>	<b>9676.333</b>	
		N	1 set	<b>9676.234</b>	<b>9676.334</b>	
	3	L1, L2, L3	1 set	<b>9676.235</b>	<b>9676.335</b>	
120	2	L1, L2, L3	1 set	<b>9676.236</b>	<b>9676.336</b>	
		N	1 set	<b>9676.237</b>	<b>9676.337</b>	
	3	L1, L2, L3	1 set	<b>9676.238</b>	<b>9676.338</b>	
<b>B Contact makers</b> for Flat-PLS						
For busbar width B mm	Screw	No. of strands per conductor	Packs of			
60	1)	2	1	<b>9676.526</b>	<b>9676.526</b>	
60	1)	3 or 4	1	<b>9676.546</b>	<b>9676.546</b>	
80	1)	2	1	<b>9676.528</b>	<b>9676.528</b>	
80	1)	3 or 4	1	<b>9676.548</b>	<b>9676.548</b>	
100	1)	2	1	<b>9676.520</b>	<b>9676.520</b>	
100	1)	3 or 4	1	<b>9676.540</b>	<b>9676.540</b>	

1) Must be ordered additionally according to the busbar width B (length = B + 40 mm, see page 335).



## Rittal France

RITTAL SAS  
 ZA des Grands Godets · 880 rue Marcel Paul  
 94507 Champigny sur Marne Cedex  
 Phone: +33 (0) 1 49 83 60 00  
 Fax: +33 (0) 1 49 83 82 06  
 E-mail: info@rittal.fr · www.rittal.fr