



System accessories Page 507 **Cable entry** Page 650

Material and surface finish:

- Enclosure frame: Stainless steel 1.4301 (AISI 304), 1.5 mm, uncoated
- Roof: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed, grain size 400
- Door: Stainless steel 1.4301 (AISI 304), 2 mm, exterior brushed, grain size 400
- Rear panel: Stainless steel 1.4301 (AISI 304), 1.5 mm, exterior brushed, grain size 400
- Base: Stainless steel 1.4301 (AISI 304), 1.5 mm, uncoated
- Mounting plate: Sheet steel, 3 mm, zinc-plated

Protection category IP to IEC 60 529:


- IP 66

Protection category NEMA:

- NEMA 4X

Supply includes:

- Enclosure frame with door
- Roof
- Base, solid
- Rear panel
- Mounting plate
- 4 eyebolts
- Lock: 3 mm double-bit



IP 66/NEMA 4X

Width (B) mm	Packs of	800	Page
Height (H) mm		2000	
Depth (T) mm		600	
Mounting plate width (F) mm		699	
Mounting plate height (G) mm		1896	
Model No.	1 pc(s).	8450.680	
Door(s)		1	
Accessories			
Side panels, screw-fastened, stainless steel	2 pc(s).	8700.060	534
Baying frame IP 66/NEMA 4, NEMA 4X	1 pc(s).	8700.010	535
Base/plinth trim panels, side, 100 mm	1 set(s)	8701.060	518
Base/plinth components, front and rear, 100 mm	1 set(s)	8701.800	518
Base/plinth trim panels, side, 200 mm	1 set(s)	8702.060	518
Base/plinth components, front and rear, 200 mm	1 set(s)	8702.800	518
Base/plinth trim, modular	4 pc(s).	2913.000	518
Quick-fit baying clamp, one-piece	6 pc(s).	8800.500	543
Baying clamp, horizontal	4 pc(s).	8800.400	543
Angular baying bracket	4 pc(s).	8800.430	545
Rail systems		from page	605
Cable duct for vertical TS section		see page	663
Cable duct		see page	673
Cable clamp rails	2 pc(s).	4192.000	665
Sheet steel wiring plan pockets	1 pc(s).	4118.000	578
System lights		from page	634
Lock systems		from page	563