

Interior installation

Assembly components

Spring nut M5

For

- Comfort Panel from an installation depth of 74 mm
- Optipanel from an installation depth of 100 mm
- Compact Panel

The spring ensures reliable protection against unintentional displacement.

Other interior installation, e.g. with

- Mounting bracket 4597.000 (see page 617) or
- Mounting bracket for interior installation 6205.100 (see page 617)

Material:

- Sheet steel, zinc-plated

Packs of	Model No.
50 pc(s).	6108.000



Threaded inserts M6

for KS

For securing installed equipment to the moulded bosses in the door and in the enclosure rear panel. Screw length available for insertion: 8 mm.

Packs of	Model No.
20 pc(s).	1482.000



Multi-tooth screws

M6 x 12 to fit:

- Snap-on nuts (8800.806)
- U nuts for punched rails (4179.000)
- Captive nuts (4164.000)
- Threaded blocks (4162.000)

M8 x 12 to fit:

- Snap-on nut (8800.808)

Multi-tooth drive for optimum transmission of torque, an extended tool life and increased safety and reliability when tightening and loosening screw connections.

Type of screw	Size mm	Packs of	Model No.
Multi-tooth screws	M6 x 12 M8 x 12	300 pc(s). 300 pc(s).	2504.500 2504.800
Metal multi-tooth screws	5.5 x 13	300 pc(s).	2486.500
Metal multi-tooth screws for stainless steel	5 x 13	300 pc(s).	2486.300
Self-tapping screws:			
■ Hex screws	M5 x 10	500 pc(s).	2504.000
■ Posidrive raised countersunk screws	M5 x 12	500 pc(s).	2488.000
■ Pan-head screws, posidrive	M5 x 12	500 pc(s).	2489.000
■ Multi-tooth pan-head screws	M5 x 12	500 pc(s).	2489.500
Self-tapping screws	ST 4.8 x 16	300 pc(s).	2487.000



Metal multi-tooth screws

For the round holes 4.5 mm diameter in the enclosure section, punched rails and punched sections without mounting flanges.



Self-tapping screws

For the round holes 4.5 mm diameter in the enclosure section, punched rails and punched sections without mounting flanges.



Self-tapping screws

Mark, drill and tighten in a single operation using electric or pneumatic tools.

For metal thickness: 0.8 – 3 mm

Length: 16 mm

Usable length: 9.5 mm

Width across flats: 8 mm

