

RiLine accessories

for RiLine60 CB component adaptors



Insert strip

for circuit-breaker component adaptors

To extend the construction width from 140 mm to 190 mm.

Material:
ABS

Colour:
RAL 7035

| For circuit-breaker component adaptor | Width mm | Approvals | Packs of | Model No. SV |
|---------------------------------------|----------|-----------|--------------|-----------------|
| SV 9342.700 SV 9342.710 | 25 | UL | 4 (1 set) | 9342.720 |

Note:

4 units (1 set) are needed to widen a component adaptor.



Sliding blocks

for circuit-breaker component adaptors

For additional locking of circuit-breakers with more than two attachment points.

Colour:
RAL 7035

Note:
UL approval in conjunction with circuit-breaker component adaptor.

| For circuit-breaker component adaptor | With threaded insert | Packs of | Model No. SV |
|--|----------------------|----------|-----------------|
| SV 9342.500/.510 SV 9342.504/.514 SV 9342.540/.550 | M3/M4 | 6 | 9342.560 |
| SV 9342.600/.610 SV 9342.604/.614 | M4/M5 | 6 | 9342.640 |



Connection bracket

for circuit-breaker component adaptors

Pre-assembled, laminated flat copper for connecting standard, commercially available moulded case circuit-breakers (MCCB).

Material:

Electrolytic copper F20

Insulation:

- Vinyl compound
- Temperature resistant to 105°C
- Fire protection corresponding to UL 94-V0

Detailed drawings:

Available on the Internet.

| Dimensions ¹⁾ mm | For circuit-breaker component adaptor | For connecting moulded case circuit-breakers (MCCB), make (model) | Packs of ²⁾ | Model No. SV |
|-----------------------------|---------------------------------------|---|------------------------|------------------------------|
| 6 x 9 x 0.8 | SV 9342.500/.510 SV 9342.540/.550 | ABB (T1, T1 UL, T2, T2 UL), Eaton (NZM1, NZM1 UL, BZM B1), OEZ (BC160N), Schneider Electric (NSC100, NSE75, NSE100) Siemens (3RV13 53, 3VT 1) | 3 | 9342.570³⁾ |
| 10 x 15.5 x 0.8 | SV 9342.600/.610 | ABB (T3, T3 UL), GE (FE), Schneider Electric (NSF150, NSF250) | 3 | 9342.660 |
| | | Allen Bradley (140U-J), Schneider Electric (NS/NSX100/160/250, GV7) | 3 | 9342.670 |
| | | ABB (S3), Eaton (NZM2, NZM2 UL, BZM B2), Siemens (VL250, VL250 UL) | 3 | 9342.680 |
| | | Siemens (VL150X UL, VL150 UL, VL160X, VL160) | 3 | 9342.690 |
| 10 x 32 x 1 | SV 9342.700/.710 | ABB (T5, T5 UL), Siemens (3RV10 73, 3RV13 73/74) | 3 | 9342.770 |
| | | ABB (S5), Allen Bradley (140U-L), Schneider Electric (NS/SX 400/630, NSJ 400/600) | 3 | 9342.780 |
| | | Eaton (NZM3, NZM3 UL) | 3 | 9342.790 |

¹⁾ Number of lamina x lamina width x lamina thickness

²⁾ 3 pieces = 1 set

³⁾ Universal application for switchgear with a dimensional difference between the mounting level and the upper edge of the contact level of 20 ± 5 mm.



Support rail 35 x 15 mm

For

- Circuit-breaker component adaptor
- Mini-PLS component adaptor

Material:
Sheet steel

Surface finish:
Zinc-plated

Supply includes:
Assembly screws and side anti-slip guard.

| For component adaptors | Width mm | Approvals | Packs of | Model No. SV |
|---|----------|-----------|----------|-----------------|
| SV 9342.400 SV 9342.410 SV 9629.000 | 72 | UL | 5 | 9320.120 |