



SF35

SUNFLEX® 
– wall systems –

Slide and Turn System:

Product-Discription:

- Aluminum slide and turn system with vertical profiles between the panels.
- The visible profile width of the panel joint is less than 1 9/16".
- The weight is carried by the top track -> top hung.
- The sill is available as a raised or flush sill.
- The system is working with individual non connected panels.

Mechanism:

- All components are specially designed from and for SUNFLEX only.
- All materials used are chosen for a long term use of the system, which ensures a long lifetime.

Sealings:

- Two brush pile lines horizontal between panel and tracks.
- Two non visible brush pile lines vertical between the panels.

Drainage:

- Fully integrated track-drainage.

Glazings:

- The system can be provided with all types of glass within 6/8" and 7/8" thickness.

Possible Geometries:

- The track can be straight or segmented with angles between 90° - 180°.

Available Features:

- All necessary features like panel catches, latch locks and so on are available.
- Fix panels or higher bottom rails are also available.
- etc.

Available colors:

- The profiles and the hardware are available in a large color range.
- The profiles can be anodised, powder coated or wet painted.
- Marine environment finish for powder coatings is also available.