


Rated current max. 65 A, with connection cables

						
Rated current max. A	Packs of	65	65	65	65	Page
Rated operating voltage V, ~		690, 3~	690, 3~	690, 3~	690, 3~	
Number of poles		3-pole	3-pole	3-pole	3-pole	
Connection cables, design		AWG 6	AWG 6	AWG 6	AWG 6	
Connection cables, length mm		130	130	130	130	
With support frame mm		–	55 x 170	55 x 237	–	
With support frame support		–	–	■	–	
With PinBlock		–	–	–	–	
With insert strips		–	–	–	■	
Support rails Qty/height mm		1 / 10	1 / 10	2 / 10	1 / 7.5	
Support rail version		TS 55E	TS 55E	TS 55E TS 55D-V	Metal	
Width mm		55	55	55	75	
Height mm		208	208	272	208	
Approvals		UL	UL	UL	UL	
For bar systems with centre-to-centre spacing mm		60	60	60	60	
For bar thickness mm		5/10	5/10	5/10	5/10	
<b>Model No.</b>	1 pc(s).	<b>9340.410</b>	<b>9340.430</b>	<b>9340.450</b>	<b>9340.700</b>	
<b>Accessories</b>						
Connection pin	20 pc(s).	9340.280	9340.280	9340.280	–	260
Insert strip	2 pc(s).	9340.290	9340.290	9340.290	–	259
Support rails		from page	from page	from page	from page	259
OM supports		see page	see page	see page	see page	225
PinBlock	5 pc(s).	–	9342.810	9342.810	–	260

Accessories



**Rittal - The System.**  
Faster - better - sustainable.

**Rittal Power Engineering 6.1**  
BY 883.000

**Rittal Power Engineering 6.1**  
Empowering Your Power Distribution Infrastructure with Software and Services

## Power Engineering

see page 295