

RiLine accessories

Busbars



CUPONAL busbars

To DIN EN 13 601

Length: 2400 mm/bar

Copper-coated aluminium busbars, suitable for the configuration of busbar systems with busbar supports 9340.000/9340.050, see page 212.


Material:

- Aluminium core with crimped copper coating made from E-Cu


Dimensions mm	Rated current ¹⁾ A	Packs of	Model No.
20 x 5	235	6 pc(s).	3582.020
20 x 10	363	3 pc(s).	3585.020
30 x 5	328	6 pc(s).	3584.020
30 x 10	493	3 pc(s).	3586.020

¹⁾ Current carrying capacity at 65°C bar temperature and 35°C ambient temperature
Correction factor diagram to DIN 43 671

Short-circuit resistance diagrams



CUPONAL busbars mm	Busbar support	Curve
30 x 5/10	9340.000/050	a
20 x 5/10	9340.000/050	b



Busbars E-Cu

To DIN EN 13 601

Length: 2400 mm/bar

Material:

E-Cu F30

Technical details:

Available on the Internet

Dimensions mm	Approvals	Packs of	Model No.	Page
12 x 5	UL	6 pc(s).	3580.000	
15 x 5	UL	6 pc(s).	3581.000	
20 x 5	UL	6 pc(s).	3582.000	
25 x 5	UL	6 pc(s).	3583.000	
30 x 5	UL	6 pc(s).	3584.000	
12 x 10	UL	6 pc(s).	3580.100	
15 x 10	UL	6 pc(s).	3581.100	
20 x 10	–	3 pc(s).	3585.005	
30 x 10	–	3 pc(s).	3586.005	
40 x 10	–	3 pc(s).	3587.000	
50 x 10	–	2 pc(s).	3588.005	
60 x 10	–	2 pc(s).	3589.005	
80 x 10	–	1 pc(s).	3590.005	
100 x 10	–	1 pc(s).	3590.015	

Accessories

Busbar connectors for busbars mm	12 x 5 – 15 x 10 (single connection)	3 pc(s).	9350.075	254
	20 x 5 – 30 x 10 (single connection)	3 pc(s).	9320.020	254
	20 x 5 – 30 x 10 (bayed connection)	3 pc(s).	9320.030	254
Busbar cover sections for busbars mm	12/15 x 5	4 pc(s).	9350.010	253
	12/15 x 10	4 pc(s).	9350.060	253
	12 x 5 – 30 x 10	10 pc(s).	3092.000	253
	40 – 60 x 10	10 pc(s).	3085.000	253